



MSR Gold™ 2500/2 FastFit ICT

Product family description

FastFit is also available in MSD Gold™, Ceramic ST and Halogen.

Product Features

- Philips FastFit
- Very short arc
- Compact design
- Flexible power range
- Philips pinch protection
- Innovative gold plated pins
- MSR filling

Product Benefits

- Lamp replacement in just seconds, exchangeable with halogen lamp
- High beam intensity
- Easy handling, smaller and lighter fixtures possible
- Boostable light levels
- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Reduces early lamp or lamp holder failures. Excellent current transfer
- Pure, white light; color point close to black body line

Product data	
Order code	827279 00
Full product name	MSR Gold™ 2500/2 FastFit ICT
Packing type	1 Carton
Pieces per pack	1
Net weight per piece	0.150 KG
Successor order code	
System Description	FastFit
Cap-Base	PGJX50
Cap-Base Information	PGJX50
Execution	-
Operating Position	any
Main Application	Entertainment
Packing Type	ICT [1 Carton]

PHILIPS

Product data	
Packing Configuration	4
Life to 50% failures EM	750 hr [nom]
Lamp Wattage	2500W
Technical Type	2500
Lamp Wattage Technical	2500 W [nom]
Lamp Current	19.53 A [nom]
Ignition Supply Voltage	198 V [min]
Dimmable	Yes
Color Code	2
Color Rendering Index	85 Ra8 [nom]
Color Temperature	7200 K [nom]
Color Temperature Technical	7200 K [nom]
Chromaticity Coordinate X	301 - [nom]
Chromaticity Coordinate Y	325 - [nom]
Luminous Flux Lamp EM	187500 Lm [min] 193000 Lm [nom]
Luminous Efficacy Lamp EM	77 Lm/W [nom]
Base Face to Base Face A	- mm [max]
Overall Length C	153 mm [max]
Diameter D	35.5 mm [max]
Diameter DI	- mm [nom]
Width F	41 mm [nom]
Light Center Length L	73.9 mm [min] 74.9 mm [nom] 75.9 mm [max]
Arc Length O	9.5 mm [nom]
Pinch Temperature	500 C [max]
Bulb Temperature	950 C [max]





MSR Gold™ FastFit

**MSR Gold 1200W/1500W/2000W/2500W/700W PGJX50/
PGJX50-K**





MSR Gold™ 1200 FastFit



Operating Position any

Cap-Base PGJX50



MSR Gold 2500/2 FastFit

MSR Gold 2500/2 FastFit



MSR Gold™ FastFit

MSR Gold PGJX50/PGJX50-K

	A	A	A	A	A	A
Full product name	Min	Min	Nom	Nom	Max	Max
MSR Gold™ 2500/2 FastFit ICT	-	-	-	-	-	-

	C	C	D	D	D1	D1
Full product name	Max	Max	Max	Max	Nom	Nom
MSR Gold™ 2500/2 FastFit ICT	153	153	35.5	35.5	-	-

	F	F	F	F	F	F
Full product name	Min	Min	Nom	Nom	Max	Max
MSR Gold™ 2500/2 FastFit ICT	-	-	4l	4l	-	-

	L	L	L	L	L	L
Full product name	Min	Min	Nom	Nom	Max	Max
MSR Gold™ 2500/2 FastFit ICT	73.9	73.9	74.9	74.9	75.9	75.9

	O	O
Full product name	Nom	Nom
MSR Gold™ 2500/2 FastFit ICT	9.5	9.5



©2009 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Document order number : 0000 000 00000